OSRAM XENARC NIGHT BREAKER LASER (NEXT GEN)

Brightest OSRAM xenon light





Up to 220% more brightness1), 2) More light allows to see farther and therefore react sooner compared to the minimum legal standard



Up to 250 m long beam

For better visibility



Up to 20% whiter light1)

More modern look compared to the minimum legal standard



For more customer satisfaction

3 year guarantee, refer to www.osram.com/amguarantee for precise conditions



The most powerful xenon light from OSRAM

XENARC NIGHT BREAKER LASER is the brightest OSRAM xenon light. This powerful lamp with efficient xenon technology ensures a better visibility on the road: up to 220% more brightness compared to the minimum legal standard. More light allows to see further and therefore react sooner. Added to this is the up to 250 meter long beam and up to 20% whiter light for more modern look (compared to the minimum legal standard). Discover the pure performance of XENARC NIGHT BREAKER LASER - the most powerful xenon light from OSRAM, available in D1S, D2S, D3S and D4S. Please note: XENARC lamp change is recommended to be carried out by a professional and in pairs.1) Compared to minimum ECE R98/R99 requirements2) D3S, D4S

Technical data

	Product information	Electrical data				
Product description	Product legal advice 1	Product legal advice 2	Power input	Nominal voltage	Nominal wattage	Power input toleranc e
XENARC NIGHT BREAKER LASER D1S	1) Compared to minimum ECE R98/R99 requirements	2) D3S, D4S	35 W	85.0 V	35.00 W	±3 %
XENARC NIGHT BREAKER LASER D2S	1) Compared to minimum ECE R98/R99 requirements	2) D3S, D4S	35 W	85.0 V	35.00 W	±3 %
XENARC NIGHT BREAKER LASER D3S	1) Compared to minimum ECE R98/R99 requirements	2) D3S, D4S	35 W	42.0 V	35.00 W	±3 %
XENARC NIGHT BREAKER LASER D4S	1) Compared to minimum ECE R98/R99 requirements	2) D3S, D4S	35 W	42.0 V	35.00 W	±3 %

		Photomet rical data	Dimensions & weight		Lifespan		Additional product data
Product description	Test voltage	Luminous flux	Length	Diameter	Lifespan B3	Lifespan Tc	Base (standard designation)
XENARC NIGHT BREAKER LASER D1S	13.5 V	3200 lm	83.2 mm	9 mm	1500 h	3000 h	PK32d-2
XENARC NIGHT BREAKER LASER D2S	13.5 V	3200 lm	77.3 mm	9 mm	1500 h	3000 h	P32d-2
XENARC NIGHT BREAKER LASER D3S	13.5 V	3200 lm	83.2 mm	9 mm	2000 h	3000 h	PK32d-5
XENARC NIGHT BREAKER LASER D4S	13.5 V	3200 lm	77.3 mm	9 mm	2000 h	3000 h	P32d-5

	Capabilities	Certificates & standards	Environmental information Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACh)	
Product description	Technology	ECE category	Date of Declaration	Primary Article Identifier
XENARC NIGHT BREAKER LASER D1S	HID ²⁾	D1S ³⁾	12-04-2024	4052899631281 4052899631328
XENARC NIGHT BREAKER LASER D2S	HID	D2S ³⁾	08-03-2024	4052899631298 4052899631335
XENARC NIGHT BREAKER LASER D3S	HID	D3S ³⁾	08-03-2024	4052899631304 4052899631342
XENARC NIGHT BREAKER LASER D4S	HID	D4S ³⁾	08-03-2024	4052899631311 4052899631359

Product description	Declaration No. in SCIP database
XENARC NIGHT BREAKER LASER D1S	In work
XENARC NIGHT BREAKER LASER D2S	In work
XENARC NIGHT BREAKER LASER D3S	In work
XENARC NIGHT BREAKER LASER D4S	In work

 $^{1)}$ Reduced UV emission/For projection headlights/ECE approval and DOT label

²⁾ High-intensity discharge lamp

³⁾ To be operated only with approved electronic control gear

File

Download Data



Movie application

Installation Video Xenarc Night Breaker Laser Opel Zafira (EN)

Safety advice

XENARC lamps should be replaced by a qualified mechanic.

This product must only be operated with approved electronic control gear.

Legal advice

Light output compared to the minimum ECE R98/99 requirements

This product must only be operated with approved electronic control gear

XENARC lamps should be replaced by a qualified mechanic

Reduced UV emission | For projection headlights | ECE approval and DOT label

± 450 lm

Application advice

For more detailed application information and graphics please see product datasheet.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.